


LAS1606 COMPRESSION SEAL FITTING GUIDE



LENGTH _____

CONTENTS

- Kerf-fit LAS1606 seal

TOOLS REQUIRED

- Tape measure
- Pencil or marker
- Scissors, knife or snips
- Router + 3mm cutter

NOTE

Recommendations as to methods, use of materials and construction details are based on the experience and knowledge of Lorient and are given in good faith as a general guide and service to designers, contractors and manufacturers.

Lorient reserves the right to make alterations or delete any installation detail without prior notice.

INSTALLATION DETAIL

NOTE

Fitting the LAS1606 seal requires a 2mm wide x 6mm (min) deep groove. Min/max recommended gap size is 3mm/6mm. The LAS1606 is designed as a push-fit seal.

STEP 1

Measure door frame opening and cut timber door stops to suit.

STEP 2

Using a router, machine a 2mm wide x 6mm (min) deep groove along the door stop.

STEP 3

Clean out the routed groove ensuring that it is free of sawdust.

STEP 4

Measure and cut the LAS1606 to the desired length allowing an additional 50mm.

STEP 5

Starting from one end and ensuring that the gasket is not stretched, offer the kg of the LAS1606 to the groove and push it into place working progressively down the door stop. Trim off excess seal.

STEP 6

Bring the door to the anticipated closed position and mount the stop so that there is a small amount of compression on the seal bulb.

Do not over compress seal as this will increase door latching forces.

STEP 7

Repeat with the head and jambs and check final operation of the door.

NOTE

Ensure that the installation of this product does not impede the opening or closing of the door. It is recommended to check the door seal periodically to ensure the door assembly to which it is fitted, closes and latches properly.

The seal may be cleaned periodically with a damp cloth and mild detergent.



V1



Lorient Polyproducts Ltd
Endeavour House
Fairfax Road
Heathfield Ind Estate
Newton Abbot
Devon TQ12 6UD
United Kingdom

+44 (0)1626 834252
www.lorientgroup.com

All rights reserved. No part of this fitting guide may be reproduced, stored in a retrieval system, or transmitted in any means, electronic, mechanical, photocopying, recording or otherwise without the written permission of Lorient Polyproducts Limited. © Lorient Polyproducts Ltd 2018